


## Plastic cabinet for HWM manifolds



The cabinet was designed to improve the aesthetics of the installation and protect it from external factors. It is equipped with the necessary brackets and a set of screws for stable mounting of the manifold. Knockout holes located on each wall provide ample cable routing and facilitate adapting the installation method to the installation conditions. The cabinet is available as a flush-mount version.

Type	Catalog number
Plastic cabinet for HWM manifolds – 4 distribution points	210952
Plastic cabinet for HWM manifolds – 6 distribution points	210953
Plastic cabinet for HWM manifolds – 8 distribution points	210954
Plastic cabinet for HWM manifolds – 10 distribution points	210955

### Dimensions



Type	External dimensions						
	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	G [mm]
Plastic cabinet for HWM manifolds – 4 distribution points	290	330	88	320	360	10	300
Plastic cabinet for HWM manifolds – 6 distribution points	310	430	88	340	460	10	409
Plastic cabinet for HWM manifolds – 8 distribution points	330	530	88	360	560	10	500
Plastic cabinet for HWM manifolds – 10 distribution points	330	625	88	360	660	10	590
Type	Internal dimensions						
	A [mm]	B [mm]	C [mm]				
Plastic cabinet for HWM manifolds – 4 distribution points	280	320	80				
Plastic cabinet for HWM manifolds – 6 distribution points	300	420	80				
Plastic cabinet for HWM manifolds – 8 distribution points	320	520	80				
Plastic cabinet for HWM manifolds – 10 distribution points	320	615	80				